


Assembling - Maintenance

This drawing is appendix A of the installation and maintenance instruction "Pneumatic Valve 2.0".


Complete installation and maintenance instruction refer to QR-Code or:

<https://www.allfi.com/en/services/downloads/product-manuals/>

- Pressure relief holes must not be covered or closed.



A-A





Pneumatic

Pressure: 6 bar / 88 psi

Hose-Ø: 8 mm

Detail B (1 : 1)



Sealing kit 2.0
912050
Including Pos.
2,3,4,5,6



*) -> Assembly-Grease DX
Allfi-Art.: 051055

Item	Qt	Description	Part-Number	Comments	Weight
1	2	Pneumatic cylinder 2.0 NC	912190		2293.9 g
2	2	Needle complete 2.0	912076	Wear part	2.2 g
3	2	Spring	021033		0.1 g
4	2	Pressure plate 2.0	912053	Wear part	11.8 g
5	2	HP-Seal 2.0	912052	Wear part	1 g
6	2	Conical disc 2.0	912062		0.4 g
7	1	Valve Body 3-Way 2-Stem 9/16" 2.0 Imp	912072-I	Wear part	1775.9 g
8	3	Collar 9/16"	719100		28.9 g
9	3	Gland Nut 9/16" Imp	709107		111 g

General tolerances ISO 2768-1 mK Designs and drawings created and produced by the contractor are the contractor's intellectual property and may only be used for the purposes of the order. Weight 6.81 kg

Amendment:	Replace for:	-
	Replaced by:	-
	Drawn	12.09.2017 AM
	Checked	08.04.2025 PH
	Release	08.04.2025 PH
	Index-release	

Pneum. 2-stem valve 9/16" NC 2.0 Imp

Scale
1 : 2

Max 4150 bar / 60,000 psi
Normally closed



ALLFI AG - RIEDENMATT 1 - CH-6370 STANS

PHONE +41(0)41-618 05 05

E-MAIL: sales@allfi.com

<http://www.allfi.com>

911170-I

Index	Sheet-	2
	No.	
	No. of	2
	sheets	

